

Technical Specification			
Ventilation Modes			
	A/C-V with Sigh	A/C-P	
	SIMV-V	SIMV-P	
	SPONT/PSV	CPAP	MANUAL
Parameters			
• Tidal Volume:	0~2000 ml		
• Respiration Rate:	1~120 bpm (A/C mode)		
	1~40 bpm (SIMV mode)		
• I:E Ratio:	1:10~4:1		
• FiO ₂ :	40%~100%		
• Trigger Sensitivity:	Pressure trigger: -20~0 cmH ₂ O		
• Flow Trigger:	2~30 L/min		
• PEEP:	0~30 cmH ₂ O		
Monitoring			
• Pressure Value:	Ppeak, PEEP		
• Volume / Flow Value:	Vt, MV		
• Time Value:	ftotal		
• Real Time Curves:	Pressure-Time, Flow-Time		
Alarms			
	Paw high	Paw low	MV high
	MV low	FiO ₂ high*	FiO ₂ low*
	No Vt	CP high	O ₂ deficiency
	Apnea	EX. power lost	Battery low
Technical Data			
• Supply Gas:	O ₂ , 0.25~0.6 MPa		
• Power Supply:	AC100~240 V, 50 Hz/60 Hz, ≤65 VA		
• Screen Size:	5" LCD Screen		
• Maximum Security Pressure:	≤8 kPa		
• Dimension (WxDxH):	168 mm x 156 mm x 300 mm		
• Battery Operating Time:	Approx. 4.5 hrs		
• Weight:	3.2 kg (Main unit)		
	8 kg (Main unit & Accessories)		



Shangrila510S

Emergency Transport Ventilator

CE 0123

AEOMED
Reliable Quality Thoughtful Service

The information contained in this leaflet is correct at the date of publication. The policy of Beijing Aeonmed Co., Ltd. is one of the continued improvement to its products. Because of this policy, Aeonmed reserves the right to make any change, which may affect the information in this leaflet without giving prior notices. The * marked accessories/ functions are optional.

HQ: Building 9, No.26 Outer Ring West Road, Fengtai District, Beijing 100070, China
Science Park: No. 10, Chaobai Street, Yanjiao Development Zone, Sanhe City, Hebei Province 065201, China
TEL: +86-10-5841 1198 FAX: +86-10-8368 1616-8130
Http: //www.aeonmed.com/en E-mail: marketing@aeonmed.com

510S_V1.0 202509

AEOMED
Reliable Quality Thoughtful Service



Shangrila 510S
Emergency Transport Ventilator

- Combines advanced technology and versatile ventilation functions
- Meets the breathing requirements of adults, pediatric and infant patients
- Pneumatically driven electronically controlled

Features

Simple operation, compact design, reliable performance



- Waveform display and multi-parameter monitoring
- Electronically controlled PEEP



- Acoustic and visual alarms
- Anti-crash design



- Direct access to critical settings and patient data



- Air supply via venturi technology

Safety Guarantee

- Meets with EN1789 standard
- IPX4 waterproof level

Applications

Emergency – Transport – Intra-hospital transfer – Recovery



Multiple Ways of Power Supply

- Vehicle D/C power*
- 4.5 hrs long lasting internal battery
- A/C power

Comprehensive Accessories*

- 2.8 L Oxygen cylinder kit
- Hanging plate assembly
- Oxygen sensor



Multi-functional Emergency Transport Ventilator

- It helps optimize quality of care & patient comfort, improving patient outcomes
- One device addresses diverse ventilation requirements, fully covering various situations

Integrated with Versatile Ventilation Modes

- Pressure control & Volume control mode
- Invasive & Non-Invasive ventilation
- SPONT/PSV, CPAP modes

Manual Intervention Functions

- Manual breath
- Inspiratory hold

Enhancements

- FiO₂ 40% to 100% continuously adjustable
- Waveform display: Pressure- time, Flow-time
- Alarm silence
- Pre-use test